

MicroCare[™] SSF2 Smoothing Station Fluid II

Introduction

MicroCare SSF2 Smoothing Station Fluid II is a nonflammable fluid consisting of a hydrofluoroether and trans-1,2-dichloroethylene. It is formulated to replace n-propyl bromide and trichloroethylene when used in 3D Printing machines for smoothing. For specifics on how to use this material with your 3D printer, please refer to your machine owners manual or contact its manufacturer.

This Technical Bulletin summarizes product properties, safety, health, environmental and regulatory information related to MicroCare SSF2 Smoothing Station Fluid II. Users should also consult the product Safety Data Sheet (SDS) for additional information.

Applications

This fluid is ideally suited for use in both heated and in cold, or ambient temperature uses. It has enhanced solvency for a wide range of substrates and will readily dissolve oils, greases, waxes and cutting fluids. In addition to its uses for smoothing and removing surface irregularities in geometries generated in a 3D printer, MicroCare SSF2 Smoothing Station Fluid II has a broad range of cleaning capabilities.

See below for a list of typical soils readily removed from parts:

 Cutting Oils 	\cdot Gear Oils	 Heavy Greases 	 Hydraulic Oils
 Stamping Oils 	\cdot Mineral Oils	· Wax	· Silicone Oils & Grease

Safety/Flammability

MicroCare SSF2 Smoothing Station Fluid II exhibits no flash point.

It is not classified as a flammable liquid by NFPA or DOT:

Closed Cup Flash Point (ASTM-D93)	None
Open Cup Flash Point (ASTM-D1310)	None
Lower Explosion Limit	7.0 (% by volume)
Upper Explosion Limit	14.0 (% by volume)

Flash point data and limits of flammability in air provide the user with additional information that should be used as elements of a fire risk assessment and to define guidelines for the safe handling of volatile chemicals. Users should assure compliance with NFPA standards and local fire codes.

Material Compatibility

MicroCare SSF2 Smoothing Station Fluid II is compatible with metals. Contact with highly basic materials, pH 10 and above, is not recommended.

Plastics that may show signs of softening, swelling or other changes include acrylic, ABS and polycarbonate. Elastomers, if affected, will generally revert to within a few percent of original size after air-drying. Prior-to-use, testing of plastics and elastomers should be performed under conditions expected during normal operation (e.g., time in contact with MicroCare SSF2 Smoothing Station Fluid II, temperature, etc.).

This product has properties that make it easily recoverable by off-line or in-line distillation equipment such as a still. The presence of soils in the fluid, however, may alter the characteristics of the material during recovery operations. Recovery should be closely monitored to ensure operating levels are maintained.

Environmental Legislation

The ingredients of this formula are listed as "Acceptable" by the U.S. Environmental Protection Agency (EPA) under the Significant New Alternatives Policy (SNAP) program as a substitute for ozone depleting substances in the solvent category.

Environmental Properties

Ozone-Depletion Potential (ODP)	0
Global Warming Potential (GWP/ 100 yr. ITH)*	11
Volatile Organic Compounds (VOC, g/liter)	1209

* Based on IPCC Second Assessment Report values.

All components are listed in the TSCA inventory.

Refer to the SDS for additional regulatory information.

Safety/Exposure Limits

Data from acute toxicity studies has demonstrated that MicroCare SSF2 Smoothing Station Fluid II has low toxicity. It has a calculated AEL (Acceptable Exposure Limit) of 100 ppm based on its individual components. AEL is a manufacturer assigned airborne inhalation exposure limit that specifies time-weighed average concentrations to which nearly all workers may be repeatedly exposed without adverse effects. The calculated AEL is in accordance with ACGIH formulas for TLVs for mixtures. MicroCare SSF2 Smoothing Station Fluid II is a slight skin and eye irritant and has low acute inhalation toxicity.

Please refer to the product SDS for additional information on detailed exposure limits and toxicity-related data.

Storage/Handling

MicroCare SSF2 Smoothing Station Fluid II is thermally stable and does not oxidize or degrade during storage. Store in a clean, dry, area out of direct sunlight and other sources of heat.

Protect from freezing temperatures. Do not allow stored product to exceed 52°C (125°F) to prevent leakage or potential rupture of container from pressure and expansion.

Refer to the Safety Data Sheet (SDS) for specific handling precautions and instructions.

Specifications

Composition and specifications are detailed below.

All ingredients are listed in the TSCA inventory.

Water	< 200 ppm
Appearance	Clear, colorless
Non-volatile residue	< 10 ppm (drums) or < 50 ppm (pails)



The information set forth herein is based on data believed to be reliable. MicroCare makes no warranties express or implied as to its accuracy and assumes no liability arising out of its use by others. This publication is not to be taken as a license to operate under, nor infringe upon, any patents not herein expressly described.

MicroCare.com

MicroCare, LLC 595 John Downey Drive New Britain, CT 06051 USA Tel: +1 860 827 0626 Toll Free: 1 800 638 0125 Email: TechSupport@MicroCare.com

MicroCare U.K. Ltd Unit 4, Whitehall Court Leeds LS12 5SN UK Tel: +44 (0) 113 3609019 Email: MCCEurope@MicroCare.com MicroCare Asia Pte Ltd 102E, Pasir Panjang Road Citilink, #05-06 Singapore 118529 Tel: +65 6271 0182 Email: TechSupport@MicroCare.sg ■ For more and to do ■ visit our v

🛗 in 🗗 🎔 Follow Us!

For more information and to download SDS visit our website: MicroCare.com

ISO 9001:2015 Registered

© 2025 MicroCare. All Rights Reserved. "MicroCare", the MicroCare logo and "Discover Perfectly Clean" are trademarks or registered trademarks of MicroCare, LLC.

Rev. 25098